



This plenum rated OM3 laser-optimized multimode (LOMMF) MPO fiber array cable is ready for deployment in any multimode 50/125 MTP/MPO network and is perfect for installs in plenum space. OM3 is fully backward-compatible with existing OM2 or OM1 systems. This multimode, MPO fiber cable is comprised of 12 fiber channels within each connector. This high density MPO fiber cable is pinned out in type B format and is comprised of 12 fiber channels within each connector which is perfect when space is limited and makes it possible to run a single cable that automatically terminates 12 fibers in one easy plug-in. The push-pull release mechanism for the MPO connector is easy to engage and disengage, its latch design also prevents the plug from snagging when jumper cables are being routed.

Features & Benefits

Type B pinout

No guide pins on either MPO connector

The MPO connector has a push pull spring loaded release

Plenum rated (OFNP) Jacket

3mm jacket outer diameter

Specifications

General Info

Product Line	C2G	Color	Aqua
UPC Number	757120313137	Country Of Origin	Hong Kong
Type	Cable		

Dimensions

Cable Length	16.4 ft
--------------	---------

Technical Information

Fiber Optic Cable Type	MPO, MTP, Multimode, OM3	Jacket Material	PVC (Polyvinyl Chloride)
Jacket Application	Plenum Rated	Jacket Rating	FT6 Rated, OFNP Rated
Cable Diameter	3 mm		