



Part Number : [1200720178](#)

Product Description : Micro-Change (1/2"-20 UNF) Single-Ended Cordset, 3 Poles, C-Coded, Female (Straight) to Pigtail, 22 AWG, Yellow PVC Cable, 3.70m (12.14') Length

Series Number : 120072

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 703000D02F120




Documents and Resources

Drawings

[1200720178_sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Contains Di-(2-ethylhexyl)phthalat per ED/21/2016 (20 June 2016) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

| | |
|--------------|--|
| Status | Active |
| Category | Circular Industrial Cordsets |
| Series | 120072 |
| Description | Micro-Change (1/2"-20 UNF) Single-Ended Cordset, 3 Poles, C-Coded, Female (Straight) to Pigtail, 22 AWG, Yellow PVC Cable, 3.70m (12.14') Length |
| IP Rating | IP67 |
| Product Name | Micro-Change (1/2" - 20 UNF) |
| Protocol | PROFIBUS |
| Type | Single Ended |
| UPC | 78172553063 |

Agency

| | |
|-----|---------|
| CSA | LR6837 |
| UL | E152210 |

Electrical

| | |
|-------------------------------|------------|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum | 250V AC/DC |

Physical

| | |
|----------------------|----------------|
| Cable Diameter | 5.72mm (.225") |
| Cable Length | 3.70m (12.14') |
| Color - Cable Jacket | Yellow |

| | |
|-------------------------------|------------------------------|
| Connector End A | Micro-Change (1/2" - 20 UNF) |
| Connector End B | Pigtail |
| Coupling Style | Threaded |
| Gender | Female-Pigtail |
| Keyway | C-Coded |
| LED Indicator | None |
| Material - Cable Jacket | PVC |
| Material - Connector Body | TPE |
| Material - Contact | Copper Alloy |
| Material - Coupling Nut | Black Epoxy Coated Zinc |
| Material - O-Ring | Nitrile Rubber |
| Material - Plating Mating | Gold |
| Net Weight | 180.340/g |
| Orientation | Straight to Pigtail |
| Poles | 3 |
| Temperature Range - Operating | -20° to +105°C |
| Wire/Cable Type | UL 2661 |
| Wire Size (AWG) | 22 |

This document was generated on Dec 29, 2025