

5

4

3

2




1

D

C

B

A





SPECIFICATION

Performance level	PL2
Filter type	C
Capacitance	1000pf $\pm$ 20%
Working Voltage	100V
Current rating	7.5 A
Insulation Resistance	>1G Ω

Minimum Insertion Loss

FREQUENCY (MHz)	ATTENUATION dB
5	1dB
10	3dB
50	12dB
100	20dB
500	34dB
1000	30dB

PCB Layout, Component side



				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, male, straight, 9 Poles, with turned solder pin and fixing hole	Mo?Mstab/ Scale 1.5:1
			Detail.	8-JUL-02	CV			
36283	09/12/11	SD	Insp.	09/12/11	JB			
32802	11/07/05	JMDR	Stand.					
32234	05/10/04	TR					TB 09641227230	Blatt/ Page 1 / 1
31058	8-JUL-02	CV						
Mod.	Dat.	Name						
					HARTING EURL F-95972 Paris			