





MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

MINIATURE PRECISION LIMIT SWITCH

CATALOG LISTING

914CE31-12A




NOTES

- 1 - ZINC HOUSING FINISHED WITH GRAY PAINT
- 2 - SIDE EXIT CABLE

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — 5 LB MAX	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
DIFFERENTIAL TRAVEL — — — .004 MAX	5A 1/10 HP — 125 OR 250 VAC	ONE PLACE (.0) ±.030	
OVERTRAVEL — — — — — .118 MIN		TWO PLACE (.00) ±.015	
		THREE PLACE (.000) ±.005	
		ANGLES ±	
		WEIGHT	



914CE31-12A

M

DRAWING
NUMBER

2

ISSUE

REPLACES

RELEASE NO. PR-16350

CHECK

REVISIONS

A CO-69061
S A V 9 OCT 91

CHECK

DDM/CAD

DRAWN

CHECK

S A V 9 OCT 91