

Representative Image

## Catalog No. RB873

**Description: INSNYL RING TRM 18-14 BLT NO10 BLUE**

**UPC No 786210818795**

**Home > Connectivity & Grounding > Sta-Kon > Electrical terminals**

Nylon Insulated Ring Terminal, Length .89 Inches, Width .31 Inches, Maximum Insulation .162, Bolt Hole #10, Wire Range #18-#14 AWG, Color Blue, Copper, Tin Plated, 1,000 Pack

### Descriptors

| | |
|---|---|
| Category | Electrical terminals |
| Special Features | Self-insulated with high dieletric-strength nylon sleeves. An inner bronze insulation grip sleeve lengthens the flexing radius of the conductor and eliminates conductor creep. |

### Specifications

| | |
|---|---|
| Voltage Rating | 600 V |
| Material | Copper |
| Color | Blue |

### Classifications

| | |
|---|---|
| Brand Name | Sta-Kon |
| Standard | UL E9809 |

### Dimensions

| | |
|---|---|
| Wire Size | 18-14 AWG |

### Compliance and Certifications

| | |
|---|---|
| RoHS | RoHS3 Compliant |
| REACH | REACH 247 Compliant |
| TSCA | TSCA Section 6(h) Compliant |

| | |
|---|---|
| ETIM | EC001052 Solderless copper terminals for copper conductors |
| Flange shape | Ring shape |
| Insulation | PA |
| Colour insulation | Blue |
| Reel packaging | N |
| AWG-range | 18-14 |

by ABB



Downloaded from Arrow.com.

| | |
|---|---|
| ETIM | EC001052 Solderless copper terminals for copper conductors |
| Material | Copper |
| Surface protection | Tinned |
| Stud size (imperial) | 10 |

**Certification/Standard**

| CLASS | File Number | Class | CCN | Certificate Number | Library Number |
|---|---|---|---|---|---|
| CSA | 4503 | 622302 | N/A | N/A | N/A |
| CSA | 7222 | 622302 | N/A | N/A | N/A |
| UL | E9809 | N/A | N/A | N/A | N/A |



Downloaded from Arrow.com.