

- Follow Us
 - Facebook
 - Google+
 - Twitter
 - YouTube
 - LinkedIn
 - Weibo
 - Blog
- REGISTER / LOG IN
- .
- .
- [change]
- .



- Solutions
 - Data Center
 - Enterprise
 - Industrial Infrastructure
 - Industrial Construction/MRO
 - OEM

<p>Topics</p> <p>Energy Efficiency Cloud Computing Virtualization Infrastructure Management Network Architecture Integrated Infrastructure</p> <p>Environments</p> <p>Compute Network Operations Storage</p> <p>Offerings</p> <p>Cisco ACI Physical Infrastructure Advisory Services Intelligent Software and Hardware Energy Efficient Cabinets Copper and Fiber Systems Pre-configured Infrastructures Physical Infrastructure Foundation SynapSense</p>	<p>Topics</p> <p>Intelligent Buildings Sustainable Intelligent Buildings Wireless</p> <p>Environments</p> <p>Central Plant Entrance Facility Operations Center Telecommunications Room Work Area and Conference Rooms</p> <p>Markets</p> <p>Healthcare Government Education</p> <p>Offerings</p> <p>Audio/Visual Systems Copper Systems Fiber Systems Identification/Printers Intelligent Software and Hardware NetKey Cabling Systems Outlets Cable Routing Power and Grounding Systems Surface Raceway Solutions Zone Enclosures</p>	<p>Topics</p> <p>Cabling Infrastructure Network Architecture Network Convergence Noise Mitigation Panel Optimization Safety Security</p> <p>Environments</p> <p>Control and Telecommunications Room Factory Floor Pathways</p> <p>Markets</p> <p>Energy Machine Builder Mining and Metals Shipbuilding</p> <p>Offerings</p> <p>Advisory Services Cable and Wire Management Control Panel Systems High Speed Cabling Integrated Network Zone System Power and Grounding Systems Preconfigured Micro Data Center Safety and Security</p>	<p>Topics</p> <p>Safety Productivity Reliability</p> <p>Markets</p> <p>Engineering Procurement Construction Oil and Gas Mining and Metals MRO</p> <p>Products and Applications</p> <p>Safety and Security Power and Grounding Systems Cable Management Labeling and Identification</p>	<p>Topics</p> <p>Wire Processing Engineered Solutions Control Panels Better Connections Assembly Optimization</p> <p>Markets</p> <p>Wire Harness Contract Mfg. Commercial Transportation Heavy Equipment Renewable Energy Machine and Control Panel Builders</p> <p>Environments</p> <p>Harsh Environments Halogen Free General Purpose High Volume Heavy Duty</p> <p>Offerings</p> <p>Quick-Build Harness System</p>
---	---	--	---	--

- Products and Services

<p>Products</p> <p>Full Line PDF Product Catalogs Online Products Catalog Product Promotions Cabinets, Thermal Management, Racks and Enclosures Cable Routing and Pathways Cable and Wire Bundling Copper Systems DCIM Software and Hardware Fiber Systems Grounding Identification Power Distribution and Environmental Monitoring Safety and Security Tools Wire Routing, Protection and Insulation Wire Termination Japan Market Only Products</p>	<p>Software/Intelligence</p> <p>DCIM SmartZone Overview 6 Zone™ Methodology Data Center Management Enterprise Management Intelligent Software Intelligent Hardware Advisory Services</p>	<p>Advisory Services</p> <p>Advisory Services Overview Data Center Advisory Services Data Center Assessment Services Data Center Design Services Data Center Implementation Services Industrial Automation Services Fresh Insight Safety Services</p>
---	---	---

- Support

<p>Partner Ecosystem</p> <p>Distributors Engineering Procurement Construction Technology Partners System Integrator Partners Designers Business Partners</p>	<p>Design Tools</p> <p>Visio AutoCAD Revit Netformx SketchUp ProposalWorks/Product Wizards Integrated Architecture Builder Configuration Drawings Calculators</p>	<p>Literature Library</p> <p>Product Catalogs Articles Brochures Case Studies White Papers Installation Guides Part Drawings Add-On-Guides</p>	<p>Download Center</p> <p>Power Distribution Units Support Software/Firmware/Printers Certifications Warranty Uninterruptible Power Supply Downloads PVIQ Firmware Updates MSDS Sheets</p>	<p>Contact Us</p> <p>Contact Us Product Registration</p>
---	--	--	---	--

- About Us

<p>Overview</p> <p>Company Profile Awards Privacy Policy Sustainability Unified Physical Infrastructure World Headquarters</p>	<p>Jobs</p> <p>Jobs at Panduit</p>	<p>News and Events</p> <p>Event Calendar Media Resources Social Media What's New</p>
--	---	--

- Where to Buy
 - My Favorites
 - Bill of Materials

Search Panduit.com

Search within category



[BUY NOW](#)

[DESIGN / INSTALL](#)



FZ2ELLNLNSNM020

2-fiber OM4 LC duplex to LC duplex patch cord, low smoke zero halogen (LSZH) 1.6mm jacketed cable, with Std. IL. This part number has been obsoleted with no replacement. [Click here](#) to contact customer service for further assistance.

[Specs](#) [Documents](#)



Std. Pkg. Qty.	1	
Fiber Type	OM4 50/125µm	
Flammability Rating	Low Smoke Zero Halogen (LSZH)	
Fiber Count	2	
Connector 1 Type	LC Duplex	
Connector 2 Type	LC Duplex	
Assembly Length Range	20-29 m (66-98 ft)	
Length (ft.)	66	
Length (m)	20	
Cable Color	Aqua	
RoHS Compliancy Status	Compliant	
Min. Order Qty.	1.0000	

Unified Physical Infrastructure

- [Legal Information](#)
- [Privacy Policy](#)
- [Contact Us](#)
- [Site Map](#)
- [Where to Buy](#)
- [Jobs](#)
- [Unsubscribe](#)

