USB 3.0 SuperSpeed External 2.5 in. SATA Hard Drive Enclosure with Built-In Cable and UASP Support

MODEL NUMBER: **U357-025-UASP**







Connects a 2.5 in. SATA hard disk drive or solid state drive to your laptop, netbook or notebook computer's USB port for extra storage and fast data transfer. UASP enabled for 70% more speed with UASP host controller.

Description

The U357-025-UASP USB 3.0 SuperSpeed External 2.5 in. SATA Hard Drive Enclosure is a quick, easy way to connect a SATA HDD (Hard Disk Drive) or SSD (Solid State Drive) to your laptop, netbook or notebook's USB port. Not only does it support USB 3.0 data transfer rates up to 5 Gbps, but its UASP (USB Attached SCSI Protocol) feature reduces latency and allows it to perform up to 70% faster when connected to a UASP-enabled host controller.

Perfect for storing and sharing large files like photos, music and video files, the enclosure is compatible with 2.5-inch SATA drives up to 3 TB. Just insert the drive into the SATA connector, connect the included one-foot USB 3.0 Micro-B cable to your computer, and slide the protective cover over the drive, even when it's in use, to keep it dust-free at all times.

The U357-025-UASP accepts SATA III (6 Gbps), SATA II (3 Gbps) and SATA I (1.5 Gbps) drives, as well as USB 2.0 (480 Mbps) and USB 1.1 (12 Mbps) transfer speeds. A blue LED flashes to indicate data transfer is occurring. After thirty minutes of inactivity, the enclosure goes into hibernation mode and wakes up when activity resumes. No software, drivers or external power supply is required. Compatible with Windows, Mac and Linux.

Features

Quickly Connects a SATA Drive to Your Computer's USB Port

- Ideal for storing large files like photos, music and video files and sharing them on your laptop, netbook or notebook
- Supports USB 3.0 data transfer rates up to 5 Gbps
- Features UASP (USB Attached SCSI Protocol) for performance up to 70% faster when connected to UASP-enabled host controller
- Hibernates after 30 minutes of inactivity
- Compatible with Windows, Mac and Linux

Compatible with 2.5 in. SATA Drives Up to 3 TB

- Accepts SATA III (6 Gbps), SATA II (3 Gbps) and SATA I (1.5 Gbps) drives
- Backward compatible with USB 2.0 (480 Mbps) and USB 1.1 (12 Mbps) transfer speeds

Highlights

- Supports USB 3.0 data transfer rates up to 5 Gbps
- Works up to 70% faster when connected to UASP host controller
- Compatible with 2.5 in. SATA HDDs and SSDs up to 3 TB
- Protective cover keeps SATA drive free of dust
- Requires no software, drivers or external power supply

System Requirements

- Device with USB port (USB 3.0 required for USB 3.0 speeds)
- UASP-enabled host controller required for UASP performance
- 2.5 in. SATA HDD or SSD with 9.5 mm maximum height

Package Includes

- U357-025-UASP USB 3.0 SuperSpeed External 2.5 in. SATA Hard Drive Enclosure
- USB 3.0 Micro-B cable, 1 ft.
- Owner's manual

Downloaded from Arrow.com.

- Works with both HDDs (Hard Disk Drives) and SSDs (Solid State Drives)

Easy to Use Right from the Box
- Plug and play—no software, drivers or external power supply needed
- SATA drive slides easily into convenient slot
- Protective cover keeps dust and dirt away from sensitive SATA drives
- Blue LED indicates successful data transfer
- 1 ft. USB 3.0 Micro-B cable included

Specifications

OVERVIEW	
UPC Code	037332190000
Drives Supported	2.5" HDD and SSD
Technology	SATA/eSATA
INPUT	
Bus Powered	Yes
POWER	
Power Consumption (Watts)	5.00
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	22 PIN SATA + POWER (FEMALE)
Connector Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Read, Write, Power)
PHYSICAL	
Color	Black
Material of Construction	ABS
Cable Jacket Color	Black
Cable Length (ft.)	0.2
Cable Length (m)	0.06
Shipping Dimensions (hwd / in.)	1.89 x 7.13 x 5.04
Shipping Dimensions (hwd / cm)	4.80 x 18.11 x 12.80

Downloaded from Arrow.com.

Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
Unit Dimensions (hwd / in.)	0.591 x 4.764 x 3.071
Unit Dimensions (hwd / cm)	1.5 x 12.1 x 7.8
Unit Packaging Type	Box
Unit Weight (lbs.)	0.11
Unit Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	50° to 122°F (10° to 50°C)
Storage Temperature Range	32° to 149°F (0° to 65°C)
Relative Humidity	10% to 80% RH, Non-Condensing
BTUs	17.1 BTU/Hr
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
IP68 Rated	No
IP20 Rated	No
UASP Support	Yes
Driver Required	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Downloaded from Arrow.com.