

**Part Number :** 1201030003
**Product Description :** PROFIBUS Attachable D-Sub Connector with Diagnostics LEDs and Programming Port, 45° Angle
**Series Number :** 120103
**Status :** Active
**Product Category :** Industrial Connectors
**Engineering Part Number :** PA9D0B-42

## Documents and Resources

### Drawings

1201030003_sd.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2022)9120-DC (17 Jan 2023) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Industrial Connectors |
| Series | 120103 |
| Description | PROFIBUS Attachable D-Sub Connector with Diagnostics LEDs and Programming Port, 45° Angle |
| IP Rating | IP67 |
| Product Name | D-Sub,PROFIBUS |
| Type | Field Attachable Connector |
| UPC | 78678899265 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum | 30V |

### Physical

| | |
|---|---|
| Cable Diameter | N/A |
| Coupling Type | D-Sub |
| Diagnostics / LEDs | Yes |
| Diagnostics Port | Yes |
| Gender | N/A |
| Keyway | None |
| Material - Connector Body | Zinc Die-Cast |
| Material - Contact | N/A |
| Material - Coupling Nut | N/A |
| Material - Plating Mating | N/A |
| Net Weight | 89.811/g |
| Orientation | 45° Angle |
| Poles | N/A |

Downloaded from Arrow.com.

| | |
|---|---|
| Temperature Range - Operating | -20° to +80°C |
| Wire Size (AWG) | N/A |



Downloaded from Arrow.com.