

6

5

4

3




2

1



Rev	AWO #	Description	Date	Appr
-	1654	RELEASED	01/10/05	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED P.C.B. LAYOUT
TOLERANCE ± 0.1



SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze, Tin plated

Electrical:

Operating voltage: 12 VDC max

Current rating: 1 Amp max

Insulation resistance: 100 Mohms min @ 500 VDC

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -65°C to $+125^{\circ}\text{C}$

ADAM TECH

909 Railway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

STEREO JACK, RIGHT ANGLE

PCB MOUNT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		Holes		DATE	
.X	$\pm .10$	ØXX	$\pm .10$		
.XX	$\pm .020$	ØXXX	$\pm .015$		
.XXX	$\pm .015$	ØXXX	$\pm .010$		
APPROVALS					
DRAWN	SS	01/10/05			
CHECKED					
APPROVED					
TITLE		SIZE		REV.	
		X		-	
REF:		PART NO.			
		ASJ-44-3			
		SCALE: NTS		SHEET 1 OF 1	

A

B

C

D

A

B

C

D