

Catalog

Home > Catalog



Home > 3050-B-632-B



Swage Standoffs

Model: 3050-B-632-B

Select Finish

-0 No Plate

Select Finish

-0 No Plate

Choose a CAD format

Product Details

These standoffs are made of Brass. They are Round shaped with diameter as 1/4". The thread for this part is 6-32 and length is 7/16".

SWAGE TOOLING

±.003	S	P
.075	A	1/32
.105	B	1/16
.135	C	3/32
.165	D	1/8
.230	E	3/16
.290	F	1/4

PDF Catalog

[RAF_catalog_0097.pdf](#)

Thread	6-32
O.D.	1/4"
Shape	Round
Length (L)	7/16"
Material	Brass
RoHS	Yes
Shank Length	0.105"
Board Thickness	1/16"
Shank Diameter	0.188"
Thread Clearance	0.150"
Finish	-0 No Plate



Technical Information

Electronic Hardware Components

Engineering Data

Capabilities Brochure

Services

Distributors

Company

RAF Quality Management

Industry Links

What's New

News


About

Contact

Careers

Contact Us

Find Us



95 Silvermine Rd.
Seymour CT 06483

Downloaded from [Arrow.com](#)