



**Part Number :** [1301380030](#)

**Product Description :** Super-Safeway Multiple Outlet Coverplate, Duplex, GFCI Rectangle

**Series Number :** 130138

**Status :** Active

**Product Category :** Power Distribution

**Engineering Part Number :** 3060



---

## Documents and Resources

---

### Product Environment Compliance

#### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

#### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	Power Distribution
Series	130138
Description	Super-Safeway Multiple Outlet Coverplate, Duplex, GFCI Rectangle
Enclosure Rating	N/A
NEMA Configuration	N/A
Product Name	Super-Safeway
Type	Multiple Outlet Box
UPC	78678875036

### Electrical

Current - Maximum per Contact	15.0A
GFCI	No
GFCI Reset	N/A
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	125V

### Physical

Cord Diameter	13.59mm (.535")
Cord Grip Body Size	F2 1/2"
Cord Length	7.62m (25.0')
Cord Type	14/3 SOOW
Feed-Thru	No
Flip Lid	No
Material - Housing	Nylon
Mounting Style	Permanent
Number of Receptacles	0
Packaging Type	Carton

Receptacle Type	GFCI Duplex
-----------------	-------------

---

This document was generated on Jun 10, 2026