HellermannTyton

Specification Sheet

Part Number: CTM10C2



KR/CTM series are designed to provide stability to wire bundles.

These mounts can accommodate miniature, intermediate, or standard cross-section cable ties.

Each mount is secured with a single screw.

Cable Tie Anchor Mount, 0.58 x .37", 0.19" Hole Dia, 0.2" Max Tie Width, PA66, Black, 100/pkg

Article Number	151-30400
Type	CTM1
Color	Black (BK)
Quantity Per	pack
Product Description	Designed specifically for holding heavier cable bundles these mounting bases can be used in many industries from agriculture to truck manufacture. They offer a very secure fixing and can be used with a wide variety of heavy duty cable ties up to 8.3 mm width.
Short Description	Cable Tie Anchor Mount, 0.58 x .37", 0.19" Hole Dia, 0.2" Max Tie Width, PA66, Black, 100/pkg
Global Part Name	CTM1-PA66-BK

Downloaded from Arrow.com.

Length L (Imperial)	0.58
Length L (Metric)	14.7
Fixation Method	Screw Mount
Width W (Imperial)	0.37
Width W (Metric)	9.4
Cable Ties	T18 - T50
Height H (Imperial)	.27
Height H (Metric)	6.90
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.0
Mounting Hole Diameter D (Imperial)	0.19 "
Mounting Hole Diameter D (Metric)	4.8 mm
Mounting Hole Diameter D Max (Metric)	4.8

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66

Downloaded from Arrow.com.

Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL | ANSI/UL 746B UL | ANSI/UL 1565 UL | ANSI/UL 62275
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes

Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.