

SmartRack 6U Low-Profile Switch-Depth Wall-Mount Mini Rack Enclosure

MODEL NUMBER: SRW6U



Houses, secures and organizes switches and other rack-mount equipment in server closets, classrooms, offices and other areas with limited floor space.

Features

Switch-Depth 6U Server Cabinet Accommodates 19 in. Rack Equipment

This SmartRack® 6U rack enclosure is designed for home and office network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the SRW6U has a maximum stationary load capacity of 200 pounds (91 kilograms).

Keeps Important Equipment Secure

The reversible front door and removable side panels lock securely to help prevent damage, tampering or theft. The doors and side panels are designed for quick release, making it simple to access connected equipment and cabling with little effort. Convenient top and bottom access panels allow easy cable routing through the cabinet. The vented doors and sides, as well as vents on the top and bottom, allow generous airflow from front to rear and top to bottom to keep your equipment cool and functioning at its peak.

Easy Enclosure and Equipment Installation

This 6U server rack comes fully assembled for quick and easy deployment. Front and rear vertical rails with square mounting holes accept standard rack equipment up to 16.5 inches (419 millimeters) deep, such as network switches, routers and patch panels. Hardware is included for wall-mounting the SRW6U. You can also use the optional SRCASTER kit (sold separately) to install metal casters to the rack and roll it along a level surface.

Meets Payment Card Industry Standards

The SRW6U provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance. This is essential for companies that process, store and/or transmit credit card information.

Highlights

- 6U rack constructed from powder-coated steel that stands up to tough environments
- Houses switches, routers and other equipment up to maximum 200 lb. load capacity
- Doors and side panels lock securely to help prevent damage, tampering or theft
- Ships fully assembled for immediate deployment and equipment mounting
- Provides physical equipment and media security required for PCI DSS compliance

Package Includes

- SRW6U 6U Server Rack
- (12) M6 screws
- (12) M6 cage nuts
- (12) M6 cup washers
- Mounting hardware
- (2) Keys
- Owner's manual

Specifications

OVERVIEW

UPC Code

037332154651



Powering Business Worldwide

TRIPP LITE
SERIES

Device Compatibility	Patch Panel; Network Switch; UPS
Rack Type	Small Enclosure
PHYSICAL	
Color	Black
Rack Height	6U
Rack Depth	Shallow
Maximum Device Depth (cm)	41.91
Maximum Device Depth (in.)	16.5
Maximum Device Depth (mm)	419
Minimum Device Depth (cm)	7.62
Minimum Device Depth (in.)	3
Minimum Device Depth (mm)	76
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Shipping Dimensions (hwd / in.)	17.50 x 20.60 x 26.40
Shipping Dimensions (hwd / cm)	44.45 x 52.32 x 67.06
Shipping Weight (lbs.)	34.00
Shipping Weight (kg)	15.42
Unit Dimensions (hwd / in.)	14.500 x 23.500 x 17.500
Unit Dimensions (hwd / cm)	36.83 x 60 x 44.45
Unit Weight (lbs.)	29
Unit Weight (kg)	13.15
Weight Capacity - Stationary (kg)	91
Weight Capacity - Stationary (lbs.)	200
Number of Vertical Mounting Rails	2
FEATURES & SPECIFICATIONS	
Grounding Details	Front and Back door frames
Built-in Cable Management	No
Extra Wide	No
Locking	No
Pre-Installed Casters	No
Outdoor Use	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 60950-1
Product Compliance	RoHS; EIA/ECA-310-E; UKCA



Powering Business Worldwide

TRIPP LITE
SERIES

WARRANTY & SUPPORT

Product Warranty Period (Worldwide)	5-year limited warranty
--	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.