



[🏠 Home](#) > [Product Information](#) > [HBW271M1VTR-1010](#)

Series | Type: [HBW](#) | [SMD](#)

Part Number	HBW271M1VTR-1010	
Type	SMD	Polar
Series	HBW	
Temperature Range	-55 ~ 125	°C
Voltage	35	V, DC
Capacitance	270	μF, 120 Hz
Tolerance	-20 ~ 20	%
Diameter	10	0.5 (β)mm
Length	10	0.5 (α)mm
Tanδ	0.12	120 Hz
Leakage Current	82.5	μA, 2 min.
ESR		mΩ, Hz
Impedance/20°C	0.02	Ω, 100k Hz
Impedance/-10°C		Ω, Hz
Ripple Current		mA, Hz
Ripple Current	2000	mA, 100k Hz
Endurance	4000	Hours at 125 °C
Coating/Sleeve	PET Coating	
Packaging	Reel	
Pack Quantity	500	Pieces
Carton Quantity	5000	Pieces

Part Search

