



Part Number : [5050662222](#)
Product Description : SlimStack Board-to-Board Receptacle, 0.35mm Pitch, SSB RP Series, 0.60mm Mated Height, 2.00mm Mated Width, 22 Circuits, Armor Nail
Series Number : 505066
Status : Active
Product Category : Board-to-Board Connectors



Documents & Resources

Drawings
[5050662222_sd.pdf](#)

3D Models and Design Files
[5050662222_stp.zip](#)

Specifications
[5050660000-A06.pdf](#)
[5050669200-203.pdf](#)
[5050660000-015.pdf](#)
[5050660000-014.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|--|
| GADSL/IMDS | Compliant with Exemption 33; 44; 34 |
| China RoHS | |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2024)7663-DC (21 Jan 2025) |
| EU RoHS | Compliant per EU 2015/863 |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

| | |
|----------------|--|
| Status | Active |
| Category | Board-to-Board Connectors |
| Series | 505066 |
| Description | SlimStack Board-to-Board Receptacle, 0.35mm Pitch, SSB RP Series, 0.60mm Mated Height, 2.00mm Mated Width, 22 Circuits, Armor Nail |
| Series Name | 0.35, SSB RP |
| Application | Board-to-Board |
| Component Type | PCB Receptacle |
| Product Name | SlimStack |
| UPC | 191128261197 |

Electrical

| | |
|-------------------------------|-----------------|
| Current - Maximum per Contact | 0.3A, 3.0A |
| Voltage - Maximum | 50V AC (RMS)/DC |

Physical

| | |
|--------------------------------|--------------|
| Circuits (Loaded) | 22 |
| Circuits (maximum) | 22 |
| Color - Resin | Black |
| Durability (mating cycles max) | 30 |
| Glow-Wire Capable | No |
| Mated Height | 0.60mm |
| Mated Width | 2.00mm |
| Material - Metal | Copper Alloy |

| | |
|--------------------------------|------------------------|
| Material - Plating Mating | Gold |
| Material - Plating Termination | Gold |
| Material - Resin | Liquid Crystal Polymer |
| Net Weight | 11.153/mg |
| Number of Rows | 2 |
| Orientation | Vertical |
| Packaging Type | Embossed Tape on Reel |
| PCB Locator | No |
| PCB Retention | Yes |
| Pitch - Mating Interface | 0.35mm |
| Pitch - Termination Interface | 0.35mm |
| Plating min - Mating | 0.100µm |
| Plating min - Termination | 0.050µm |
| Polarized to Mating Part | No |
| Polarized to PCB | No |
| Temperature Range - Operating | -40° to +85°C |
| Termination Interface Style | Surface Mount |

Mates With / Use With

Mates with Part(s)

| Description | Part Number |
|---|---------------|
| 0.35mm Pitch SlimStack Board-to-Board Plugs | <u>505070</u> |

This document was generated on Apr 22, 2025