
Product Details for 3 -88637 -1



3-88637 -1

Active

Flexible Film Connectors

RoHS Compliant (Statement of Compliance)

Product Highlights:

- Housing
- 2.54 mm Centerline
- Connector Type = Standard
- 60 Positions
- Number of Rows = Dual

View all Features

Quick Links

Check Pricing & Availability
Search for Tooling
Product Feature Selector
Contact Us About This Product

Documentation & Additional Information

Product Drawings:

- HOUSING,RCPT,DBL ROW / W DETENTS,.100@22,FFC (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- 3D Model (STEP, Version AE)
- 3D Model (IGES, Version AE)
- 2D Drawing (DXF, Version AE)

List all Documents

Additional Information:

- Product Line Information

Related Products:

- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Housing
- Connector Type = Standard
- Number of Positions = 60
- Mating Type = Receptacle
- Mating Connector Lock = With
- Mating Connector Lock Type = Detent
- Mating Polarization = With
- Mounting Ears = With
- Flame Retardant = Yes
- Color = Black
- Comment = Use Extraction Tool No. 91093 -1 for round wire contacts.

Mechanical Attachment:

- Panel Attachment = With

Body Related Features:

- Centerline (mm [in]) = 2.54 [0.100]
- Number of Rows = Dual

Housing Related Features:

- Housing Material = Thermoplastic
- Housing Flammability Rating = UL 94V -0

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Terminate To = FFC Cable

Other:

- Brand = AMP

© 2006 Tyco Electronics Corporation All Rights Reserved

Downloaded from Arrow.com.