



Part Number : [2205731000](#)

Product Description : Sunshade 5-in-1 (5G/Wi-Fi/GPS) Antenna Pro, 95.00mm x 95.00mm, 1000.00mm Cables with SMA Plug Male Connectors, Bolt-Nut Mounting

Series Number : 220573

Status : Active

Product Category : Antennas



Documents & Resources

Drawings

[2205731000 sd.pdf](#)

[2205731000-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2205731000-000.pdf](#)

[2205731000-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; bis(α, α-dimethylbenzyl) peroxide; Melamine; 2-Methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one per

	D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 7(c)-I; 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Antennas
Series	220573
Description	Sunshade 5-in-1 (5G/Wi-Fi/GPS) Antenna Pro, 95.00mm x 95.00mm, 1000.00mm Cables with SMA Plug Male Connectors, Bolt-Nut Mounting
Component Type	External Antenna
Function	Signal
Product Name	Sunshade 5-in-1 Antenna Pro
Protocol	Cellular, GPS, Wi-Fi
Type	External
UPC	196823076510

Electrical

Band#1 F_End (MHz)	1602
--------------------	------

Band#1 F_Start (MHz)	1561
Band#2 F_End (MHz)	960
Band#2 F_Start (MHz)	698
Band#3 F_End (MHz)	2690
Band#3 F_Start (MHz)	1710
Band#4 F_End (MHz)	4200
Band#4 F_Start (MHz)	3300
Band#5 F_End (MHz)	5000
Band#5 F_Start (MHz)	4400
Band#6 F_End (MHz)	2500
Band#6 F_Start (MHz)	2400
Band#7 F_End (MHz)	5850
Band#7 F_Start (MHz)	5150
Band#8 F_End (MHz)	7125
Band#8 F_Start (MHz)	5925
Electrical Connectivity	Cable SMA Plug Male Connector
Peak Gain (dBi)	See Product Specification
Return Loss - S11 (dB)	< -10, < -4, < -5, < -8
Total Efficiency	See Product Specification

Physical

Cable Length	1000.00mm
Length	95.00mm
Mounting Style	Adhesive and Screw Nut
Net Weight	299.500/g
Packaging Type	PET Bag
Polarization	Linear, RHCP
Radiation Pattern	High Directivity (GPS), Omnidirectional (4G,WiFi)
Thickness	38.00mm
Width	95.00mm

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	SMA Jack Female Receptacle

This document was generated on Sep 18, 2025