



Pushing Performance  
Since 1945

# Han D R15 stift-c 2,5 mm Ag



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 000 6106
Specification	Han D R15 stift-c 2,5 mm Ag
HARTING eCatalogue	<a href="https://harting.com/09150006106">https://harting.com/09150006106</a>

## Identification

Category	Contacts
Series	Han D®
Type of contact	Crimp contact

## Version

Termination method	Crimp termination
Gender	Male
Manufacturing process	Turned contacts

## Technical characteristics

Conductor cross-section	2.5 mm²
Conductor cross-section [AWG]	AWG 14
Rated current	≤10 A
Contact resistance	≤3 mΩ
Stripping length	6 mm
Mating cycles	≥500

## Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



**Pushing Performance**  
Since 1945

## Material properties

China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	100
Net weight	0.4 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140021853
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522