BACA-AMP-154 ✔ ACTIVE

CST

TE Internal #: 1375819-1

Tin (Sn), Socket Contact, 26 – 22 AWG, 250 VAC, .13 – .33 mm² Wire, Locking Lance Contact Retention, Discrete Wire, Crimp, Phosphor Bronze, Signal

View on TE.com >

Connectors > Contacts > Connector Contacts







Contact Type: **Socket**

Contact Mating Area Plating Material: **Tin (Sn)**

Wire Contact Termination Area Plating Material: **Pre-Tin**

Operating Voltage: **250 VAC**

Contact Retention Within Housing: **With**

Features

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire

Electrical Characteristics

Operating Voltage	250 VAC

Contact Features

Contact Mating Area Plating Material Thickness	1.01 – 2.99 µm[39.76 – 117.72 µin]
Mating Square Post Dimension	.63 mm[.025 in]
Contact Type	Socket
Contact Mating Area Plating Material	Tin (Sn)
Wire Contact Termination Area Plating Material	Pre-Tin
Contact Retention Within Housing	With
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	4 A

Termination Features

Termination Method to Wire & Cable	Crimp

Downloaded from Arrow.com.

Product Terminates To	Wire & Cable

Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance

Dimensions

Compatible Insulation Diameter Range	.89 – 1.65 mm[.035 – .065 in]
Wire Size	.13 – .33 mm²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Circuit Application	Signal

Packaging Features

Packaging Method	Reel
Packaging Quantity	5500

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits

Downloaded from Arrow.com.

as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 7-2151011-7
OCEAN_2.0_SPARE_PART_KIT-042F070F




TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp




TE Part # 2151011-2
OCEAN_2.0_Applicator-S-042F070F-RSA



TE Part # 5-2151011-1
OCEAN_2.0_Applicator-S-042F070F-RSM




TE Part # 91302-1
CST-100 EXTRACTION TOOL



TE Part # 58517-4
PRO-CRIMPER II DIE SET



TE Part # 5-2151011-2
OCEAN_2.0_Applicator-S-042F070F-RSA



TE Part # 7-2836880-7
OC-042F070F-CRIMPTOOLINGKIT



TE Part # 2151011-1
OCEAN_2.0_Applicator-S-042F070F-RSM




TE Part # 58517-3
PRO-CRIMPER II TOOL W/DIE SET


Customers Also Bought




TE Part #293387-4
NECTOR S OUTLET LV-2 WHITE



TE Part #696273-2
TERM, WIRE PIN, PIDG, 22-16, T&R



TE Part #CAT-104CST-RCPHS
Receptacle Housing: 2.54mm, 1 Row, CST-100 II




TE Part #4-2176599-2
RLC73PD 2H R15 1% 1K RL

Downloaded from Arrow.com.



TE Part #CD12303001
FLCW0219-0.75-1(B011)



TE Part #6-240655-9
ANVIL



TE Part #2-730230-8
ANVIL, COMBINATION

Documents

Product Drawings

CST-100 II CONTACT TIN PLT

English

CAD Files

Customer View Model

ENG_CVM_CVM_1375819-1_C.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1375819-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1375819-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Downloaded from Arrow.com.