
Downloaded from Arrow.com.

REV.	MODIFICATION.	DATE	DRN
01	Production release	18/02/09	MT



PANEL DETAILS




FIG 1
VLP-F
(FLAT)




FIG 2
VLP-D
(DOMED)

MATL: PC, RMS-23 CLEAR	FIGURE	"A"	"B"	"C"	"D"	"E"	"F"	"G"	"H"	PANEL THICKNESS
VLP1-F-1	1	12.7 [0.50]	4.7 [0.19]	1.50 [0.06]	3 [0.12]	6.4 [0.25]	2.5 [0.10]	4.7 [0.19]	1.5 ±0.05 [0.06 ±0.002]	0.8 [0.03] TO 3 [0.12]
VLP1-F-3		16.5 [0.65]								
VLP1-F-4		21.8 [0.86]								
VLP1-F-5		26.1 [1.03]								
VLP1-D-1	2	12.7 [0.50]								
VLP1-D-3		16.5 [0.65]								
VLP1-D-4		21.8 [0.86]								
VLP1-D-5		26.1 [1.03]								
VLP2-F-1	1	12.7 [0.50]	7.5 [0.30]	2.45 [0.10]	5 [0.20]	10 [0.39]	3 [0.12]	7.5 [0.30]	2.4 ±0.05 [0.09 ±0.002]	
VLP2-F-2		15 [0.59]								
VLP2-F-3		16.5 [0.65]								
VLP2-F-4		21.8 [0.86]								
VLP2-F-5		26.1 [1.03]								
VLP2-F-6		55 [2.17]								
VLP2-D-1	2	12.7 [0.50]								
VLP2-D-3		16.5 [0.65]								
VLP2-D-4		21.8 [0.86]								
VLP2-D-5		26.1 [1.03]								
VLP2-D-6		55 [2.17]								

ALTERNATE UNITS FOR REFERENCE ONLY

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.

Richco®

ALL DIMENSIONS IN mm
GENERAL TOLERANCES ±0.25
UNLESS OTHERWISE STATED
1 DECIMAL PLACE ±
2 DECIMAL PLACES ±
ANGULAR ±1°

THIRD ANGLE

MATERIAL: POLYCARBONATE (RMS-23)	COLOUR: CLEAR
DESCRIPTION: VERTICAL LIGHT PIPE	PART No: SEE TABLE
DRG No: 08-040	NPR No: FR08-0031
SHEET SIZE A4	

DRN	DATE	CHKD	DATE	SCALE	SHEET No.
MT	10/06/08	TC	18/02/09	NTS	1 OF 1

FORM No. 0143/00