


NOTES:


- 1. PARTS ARE TO BE BULK PACKED
- 2. CRIMP CONTACTS NOT ASSEMBLED INTO CONNECTOR
- 3. ALL DIMENSIONS ARE FOR REFERENCE ONLY.

KIT PART NO.	CABLE O.D
W8880-9SG-522	0.220 - 0.250 [5.6-6.4mm]
W8880-9SG-528	0.265 - 0.285 [6.7-7.2mm]


NO. OF CONTACTS — GROMMET SIZES




FACE VIEW




ASSEMBLED KIT VIEW
W8880-9SG-522 SHOWN




WIRE VIEW




IN LINE CONNECTOR




(9) #22 SOCKET CONTACTS




GROMMET, LONG



CABLE GRIP



BACKSHELL, LONG



ASSEMBLED KIT
FOR CUSTOMER REFERENCE

CUSTOMER DRAWING

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT / INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____

DATE: _____

RoHS COMPLIANT

0A	AM	08/09/16	FIRST DRAWN	
REV.	INIT.	DATE	DESCRIPTION	
AM		08/09/16	ORIG. DRAWN BY: DATE: AM 08/09/16	
CHECKED BY:			APPROVED BY:	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			TITLE: IN-LINE CONNECTOR, KIT (9) # 22 SOCKET CONTACT, CRIMP MINI-CON-X STANDARD PRODUCT	
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			CUSTOMER: 601 E. WILDWOOD VILLA PARK, IL 60181	
UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16			PART NUMBER: W8880-9SG-5XX	
- CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			REV 0A	
FILE:	8880-9SG-XXX	DIRECTORY:	SLW	
SCALE	NTS	SIZE	B	SHEET 1 OF 1