



Part Number : [1300350122](#)

Product Description : Mini-Change H-Splitter, 4 Pole, Male/Female with Female Drop, Yellow

Series Number : 130035

Status : Active

Product Category : Industrial Tees and Splitters

Engineering Part Number : DCAUXH


Documents and Resources

Drawings

[1300350122_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Reviewed per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023) SCIP:8f39b826-51ef-4d25-83fe-5fa1b7b408a0
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	130035
Description	Mini-Change H-Splitter, 4 Pole, Male/Female with Female Drop, Yellow
IP Rating	IP67
Product Name	Mini-Change
Type	H-Splitter
UPC	78172564108

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	600V AC

Physical

Color - Cable Jacket	Yellow
Drop Connector	Mini-Change
Drop Gender	Female
Keyway	Single
LED Indicator	None
Left Trunk Connector	Mini-Change

Left Trunk Gender	Male
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	TPE
Material - Coupling Nut	Zinc Die-Cast
Net Weight	321.000/g
Poles	4
Right Trunk Connector	Mini-Change
Right Trunk Gender	Female
Temperature Range - Operating	-20° to +80°C

This document was generated on May 27, 2026