



**Part Number :** 1300180230

**Product Description :** Mini-Change Shorting Plug and Closure Cap, 12-Pole, C-Size, Male, Straight, with 300.00mm Ball Link Chain

**Series Number :** 130018

**Status :** Active

**Product Category :** Connector Accessories

**Engineering Number :** BG19732



---

## Documents & Resources


### Drawings

[1300180230\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2020)9139-DC (19 Jan 2021)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	Connector Accessories
Series	130018
Description	Mini-Change Shorting Plug and Closure Cap, 12-Pole, C-Size, Male, Straight, with 300.00mm Ball Link Chain
Component Type	Shorting Plug and Closure Cap
Product Name	Mini-Change
UPC	78678804964

### Electrical

Current - Maximum per Contact	7.0A
Voltage	300V

### Physical

Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Yellow
Gender	Plug
Length	62.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	68.038/g
Polarized to Mating Part	Yes
Temperature Range - Operating	-20° to +105°C