



# HA-VIS Coax Cable SMA-N, 3m

Copper cable, (round), Pre-assembled on both sides, Low loss coax cable, Cable length: 3m, Diameter: 5.4mm

Part number: **20 93 204 0104**



## Technical data

Go to:

Identification

Technical characteristics

Material properties

Commercial data

### Identification

Category	Cable
Specification	Pre-assembled on both sides
Connector 1	N connector
Connector 2	SMA connector
Type of cable	Copper cable (round)
Description of the cable	Low loss coax cable

### Technical characteristics

Limiting temperature	-40 ... +85 °C
Cable length	3 m
Cable diameter	5.4 mm
Impedance	50 Ω

Material properties

Material (cable)	PE
Colour (cable)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Commercial data

Packaging size	1
Net weight	152 g
Country of origin	Germany
European customs tariff number	85442000
eCl@ss	27060390 Ready-made data cable (unspecified)

Alternatives



Mini Coax HA-VIS  
Coax Cable  
SMA-N 10m 20



Mini Coax HA-VIS  
Coax Cable  
SMA-N 10m 20



Mini Coax HA-VIS  
Coax Cable  
SMA-N 10m 20

✉ E-mail address

(For questions regarding products, orders and user accounts)

Website support:

✉ E-mail address

(For technical problems regarding the website)

© HARTING Technology Group

[Home](#) • [Contact](#) • [Privacy Policy](#) • [Terms of Use](#) • [Sales and delivery conditions](#) • [Cookie policy](#) • [Imprint](#)



HARTING also aims to provide you with the best possible online service; we therefore use cookies to collect visitor information and to improve our digital services. By using this website, you agree to the usage of these cookies. Detailed information and the option to object can be found in our [privacy policy](#). After clicking on "I agree", we shall also use cookies to make HARTING.com and our digital services as best as possible for your personal needs.

[I agree.](#)

