

Search within category

GO

BUY NOW

DESIGN / INSTALL

RETURN AIR



PPMA47WGD

Duct Marker, 'RETURN AIR' (legend), Green, 2.5" x 12".
Sold in US and Canada only

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Material	Dura-Polyester Vinyl			
Overall Width (mm)	304.8			
Overall Height (mm)	63.5			
Note	Sold in US and Canada only			
Application	Mark air flow and its equipment's purpose in ductwork systems			
Color	White on Green			
Diameter (mm)	152.4			
Dimensions (In.)	2.5" x 12"			
Environment	5-7 years			
Legend	RETURN AIR			
Maximum Operating Temperature (°C)	80			
Maximum Operating Temperature (°F)	176			
Maximum Overall Height (mm)	63.5			
Minimum Operating Temperature (°C)	-28			
Minimum Operating Temperature (°F)	-20			
Operating Temperature	-20°F to 176°F			
Part Features	6-mil thick poly-composite vinyl with permanent acrylic adhesive backing scored liner for quick peel-off to apply onto pipe., Sub-surface image is protected by a high-gloss UV protective coating and is resistant to abrasions, humidity, chemicals, solvents, and fading from sunlight, Includes detachable arrow to provide proper directional flow marking, 1.25" h character size, 2.5" x 12" marker for duct OD up to 6"			
UL Listed	No			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	1			
Sub Brand	SPECIALTY PIPE MARKERS			