



Home > M1579-B-4007-B-16



Metric Swage Standoffs

Model: M1579-B-4007-B-16**Select Finish**
 -0 No Plate
Request Quote[Request Custom Part](#)**RFQ**
 Choose a CAD format
Download CAD**View 3D Model****View 2D Drawing****Product Details**

These standoffs are made of Brass. They are Round shaped with diameter as 8 mm. The thread for this part is M4 and length is 12 mm.

PDF Catalog[RAF_catalog_0304.pdf](#)

Thread	M4
O.D.	8 mm
Shape	Round
Length (L)	12 mm
Material	Brass
RoHS	Yes

Shank Length	2.7 mm
Shank Diameter	5.94 mm
Thread Clearance	5.1 mm
Board Thickness (mm)	1.6
Thread Code (mm)	4,007
Finish	-16 Electro Tin



TECHNICAL INFORMATION

[Electronic Hardware Components](#)
[Engineering Data](#)

COMPANY

[RAF Quality Management](#)
[Industry Links](#)