

Part Number : 2174651052
Product Description : Ultra-Fit Tangless Female-to-Ultra-Fit Tangless Female Off-the-Shelf (OTS) Cable Assembly, 3.50mm Pitch, Single Row, 300.00mm Length, 5 Circuits, Black
Series Number : 217465
Status : Active
Product Category : Power and Signal Cable Assemblies

Documents and Resources

Drawings

2174651052_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	217465
Description	Ultra-Fit Tangless Female-to-Ultra-Fit Tangless Female Off-the-Shelf (OTS) Cable Assembly, 3.50mm Pitch, Single Row, 300.00mm Length, 5 Circuits, Black
Application	Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Ultra-Fit-to-Ultra-Fit
Product Name	Ultra-Fit
Type	Discrete Wire Assembly
UPC	195842062092

Electrical

Current - Maximum per Contact	14.0A
Voltage - Maximum	600V AC (RMS)/DC

Physical

Cable Length	300.00mm
Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Black

Downloaded from Arrow.com.

Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	High Conductivity Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	27.056/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	3.50mm
Plating min - Mating	1.524µm
Plating min - Termination	1.524µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Size (AWG)	16

Downloaded from Arrow.com.