

Specifications

Eaton DR73-R33-R



Eaton DR inductor, 0.306 uH, 6.21 A Irms, 14.4 A ISAT, 8.5 mΩ resistance, SMT mounting, Ferrite, 2-pins, 1350 qty.

Photo is representative



General specifications

PRODUCT NAME	Eaton DR73 inductor
CATALOG NUMBER	DR73-R33-R
UPC	051712888615
EAN	5027590168991
PRODUCT LENGTH/DEPTH	0.299 in
PRODUCT HEIGHT	0.14 in
PRODUCT WIDTH	0.299 in
PRODUCT WEIGHT	0.0015 lb
COMPLIANCES	RoHS Compliant

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	6.21 A
ISAT	14.4 A
PACKAGE QUANTITY	1350
MATERIAL	Ferrite
AUTOMOTIVE GRADE	No
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	8.5 mΩ
TERMINALS	7.5x7.5x3.35mm
SERIES	DR73

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton DR high power density high efficiency shielded drum core power inductors data sheet](#)

[Eaton Specification Sheet - DR73-R33-R](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

