

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
PROSPERITY, MINNESOTA

FED. MFR. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BM - 1R

BM-1R

PAGE 1 OF 1

M

DRAWING
NUMBER

910

ISSUE

(M) BM - 1R

ISSUE 1

REPLACES

RELEASE NO.

23NOV07

ASD

CHECK

26 OCT 61

26 OCT 61

26 OCT 61

26 OCT 61

26 OCT 61


26 OCT 61

26 OCT 61

26 OCT 61

26 OCT 61

26 OCT 61



NOTE
▲ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE - - - - - 7 - 10 OZ
RELEASE FORCE - - - - - 4 OZ MIN
DIFFERENTIAL TRAVEL - - - .0005 - .0010
OVERTRAVEL - - - - - .005 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T
- L 161 -
22 A - 125, 250, OR 480 VAC
1/2 HP - 125 VAC; 1 HP - 250 VAC
L288
L315
L318
22A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT
UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±
WEIGHT .050 LB

RASTER

CO-50378

DRAWN

K L B

23NOV07