

Specification Sheet

Part Number: GT.50X110P2



Features quick release for repetitive access to cable and wire.

Can be opened and closed numerous times without failure.

Adjustable so one size can accommodate multiple bundle sizes.

Grip Tie Strap, 11.0" x .5", PA6/PP, Black, 10/pkg

Article Number 854-44320

Type GT.50X11

Color Black (BK)

Quantity Per pack

Product Description The Grip Tie is a low-profile, one-piece fastening device. Constructed of a hook and loop design, laminated back to back, the Grip Tie features quick release for repetitive access to cable and wire. Reusable, adjustable, releasable, and easy to install, it can be successfully opened and closed numerous times. Grip Ties are available in a variety of colors and are versatile enough for applications ranging from network installations to bundling power cords.

Short Description Grip Tie Strap, 11.0" x .5", PA6/PP, Black, 10/pkg

Global Part Name	GT.50X11
Minimum Tensile Strength (Imperial)	40
Minimum Tensile Strength (Metric)	177.93
Length L (Imperial)	11.0
Length L (Metric)	279.4
Width W (Imperial)	0.5
Width W (Metric)	12.7
Bundle Diameter Max (Imperial)	2.63
Bundle Diameter Max (Metric)	66.802
Material	Polyethylene (PE) Polyamide 6 (PA6)
Material Shortcut	PA6 PE
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Reach Compliant (Article 33)	No
UL Recognized (US)	Yes

UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)