



**Part Number :** [368760001](#)  
**Product Description :** Ditto Hermaphroditic Crimp Terminal, High Copper, Tin Plating, 22-20 AWG  
**Series Number :** 36876  
**Status :** Obsolete  
**Product Category :** Crimp Terminals



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
--------	----------

Category	Crimp Terminals
Series	36876
Description	Ditto Hermaphroditic Crimp Terminal, High Copper, Tin Plating, 22-20 AWG
Application	Power, Wire-to-Wire
Product Name	Ditto
UPC	887191582801

## Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	350V AC/DC

## Physical

Durability (mating cycles max)	25
Gender	Hermaphroditic
Material - Metal	High Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.148/g
Packaging Type	Reel
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.70mm
Wire Size (AWG)	20, 22
Wire Size mm <sup>2</sup>	N/A

---

## Application Tooling

### Global

Description	Part Number
Extraction Tool for SPOX, MX64, Ditto, MX150CE, Milli-Grid Terminals	<u>638131400</u>
Hand Crimp Tool For Ditto Crimp Terminals	<u>638273400</u>
FineAdjust Applicator for Ditto Interconnects Terminals	<u>639030200</u>

---

This document was generated on Feb 08, 2025