



Quality Products. Service Excellence.

Heavy Duty Industrial Outlet Strip *1581 DP Series*

10A Double Pole | 100-240V | Front or Rear Facing C13 Outlets

Features



- On-Off switch is rocker type (double pole, single throw) with green light.
- Rated 100-240VAC (TUV), 120-240VAC (UL), 10 A, 50/60 Hz and designed for use with IEC power cords.
- All metal housing – tough extruded aluminum case with black powder-coated steel cover.
- Mounting feet (with keyhole slots) allow temporary work station mounting if desired.

Specifications

- One IEC 320 - C14 inlet, and 4, 5, 6 or 8 IEC 320 - C13 outlets.
- Includes 10A circuit breakers to prevent accidental line overload.
- cULus Listed UL 62368-1 (2nd Edition), 2014-12-01, and CAN/CSA C22.2 No. 62368-1-14 (2nd Edition).
- TÜV-SUD Certified to EN 62368-1:2020/A11:2020, and IEC 62368-1:2018.
- TÜV-SUD tested for EMC Compliance to EN 55032:2015+A11:2020 (CISPR 32:2015+A1:2019) & EN 55035:2017+A11:2020 (CISPR 35:2016).
- CE compliant to the European Low Voltage Directive 2014/35/EU.
- CE compliant to the European EMC Directive 2014/30/EU.
- UKCA compliant to British Electrical Equipment (Safety) Regulations 2016 (S.I. 2016/1101).
- UKCA compliant to British Electromagnetic Compatibility Regulations 2016 (S.I. 2016/1091).
- TAA compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.



Illuminated On/Off Switch Part No.	Overall Dimensions			Outlet Qty	Outlet Type	Inlet Type
	Height	Width	Length			
1581H4DP	2.33	2.13	13.75	4	C13	C14
1581H5DP	2.33	2.13	16.50	5	C13	C14
1581H6DP	2.33	2.13	16.50	6	C13	C14
1581H8DP	2.33	2.13	19.75	8	C13	C14

Replacement Mounting Foot (One Foot)

Part No.	1584MF
----------	--------



Tags: IEC

Data subject to change without notice

