

ENCLOSURE HARDWARE

LED INDICATORS

LIGHT PIPE SELECTOR

LED MOUNTS, HOLDERS

LEDs

LIGHT PIPES

BOARD MOUNT LED ASSEMBLIES


PANEL MOUNT LED ASSEMBLIES

LED LIGHTING


SOLUTIONS


RESOURCES


R2F-12.0-RED




ORCAdapt Flexible Light Pipe System, 2mm. Fiber Optic Core, 4.2mm. Dia. Flat Face Lens, 12.0in. Length, Rectangular Red LED

 Datasheet

 3D Model

 Request Samples

 RoHS Docs

FEATURES

VALUE ADDED

CHECK STOCK

- High Intensity LED, 6000mcd, Color Emitted: Red
- 4.2mm. Diameter Flat Face Lens Cap
- Flexible Light Pipe Cable Customized Length-See Specification Sheet for More Info
- Material: Flexible Light Pipe Adaptor- Nylon 6/6 94V-0, Lens Cap- Polycarbonate 94V-0 Clear
- Rear Panel Mount Lens