Specifications







Eaton CL1208-3-100TR-R

Eaton CL1208 inductor, 100 nH, 0.45 mΩ resistance, Three-phase

General specifications	
PRODUCT NAME	Eaton CL1208 inductor
CATALOG NUMBER	CL1208-3-100TR-R
UPC	051712523608
PRODUCT LENGTH/DEPTH	18 mm
PRODUCT HEIGHT	8 mm
PRODUCT WIDTH	11.5 mm
PRODUCT WEIGHT	6.25 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

TYPE	Multi-phase coupled inductor
MOUNTING	SMT
PHASE	Three-phase
ISAT	18 A
PACKAGE QUANTITY	300
MATERIAL	Ferrite
CONTACT CONFIGURATION	Six-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	0.45 mΩ
TERMINALS	Six
INDUCTANCE	100 nH
SERIES	CL1208

Resources

CATALOGS	Magnetics short form catalog
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CL1208-3-100TR-R

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.