

Home

SQF-CM8V4-240G-ECC

Phase out

BICS3 SQF M.2 2280 920 240G 3D TLC, (0~70°C)(ES)



- NGFF M.2 2280 SSD (M key)
- Compliant with PCIe Gen. III x4 interface and NVMe 1.3
- Support LDPC with RAID ECC
- TRIM 、AHCI supported
- GUI management tool & software API package

Call for Price

3Y Warranty

Make an inquiry

Resouces
[Datasheet](#) | [Download](#) | [Manual](#) | [Utilities](#) | [Extended Specifications](#) |

Specifications

Category	Attribute	Value
SQFlash	Capacity	240 GB
	Connector	M.2 M Key
	Flash Type	3D TLC BiCS 3
	Interface	PCIe / NVMe
	Operational Temperature	0 ~ 70 °C
	Shock	1,500G, Peak / 0.5 ms
	SQFlash Utility	Support
	Transfer Protocol	PCIe Gen. 3 x4
	Vibration	20G, Peak / 80 ~ 2,000 Hz