



Lexar® ARMOR SILVER PRO SDXC™ UHS-II Card

Up to 280MB/s read, up to 160MB/s write¹

- 1TB
- 512GB
- 256GB
- 128GB
- 64GB

+ Compare

Specifications



Material	Stainless steel
Capacity	64GB, 128GB, 256GB, 512GB, 1TB
Performance	64GB Up to 280MB/s read, up to 130MB/s write ¹ 128GB Up to 280MB/s read, up to 120MB/s write ¹ 256GB-1TB Up to 280MB/s read, up to 160MB/s write ¹
Form Factor	UHS-II
Video Speed Class	V60
Operating Temperature	-25° to 85°C (-13°F to 185°F)
Storage Temperature	-40° to 85°C (-40°F to 185°F)
Dimensions (W x L x H)	32mm x 24mm x 2.1mm / 1.25" x 0.95" x 0.08"
Weight	7.65g / 0.016lbs
Warranty	Limited lifetime warranty ²

¹ Up to 280MB/s read transfer, write speeds lower. Speeds based on internal testing. Actual speed may vary depending on host device.
² Limited lifetime warranty is limited to 10 years from purchase in Germany and regions not recognizing lifetime warranty.
370N Pressure Resistance
IP68 Dust and Water Resistance
5-Meter Drop-Proof
Temperature-Proof: Operation -25°to 85°C; Storage -40°C to 85°C
Wear-out resistance: up to 10,000 times of plugging and unplugging

Lexar is not liable for any loss of data or images. Product appearance, performance, software offerings, and packaging may vary depending on ship date and available inventory. Actual usable memory capacity may vary. 1GB equals 1 billion bytes.

Product Numbers



Global	Capacity	#Part
	64GB	LSDAMSP064G-RNNNG
	128GB	LSDAMSP128G-RNNNG
	256GB	LSDAMSP256G-RNNNG
	512GB	LSDAMSP512G-RNNNG
	1TB	LSDAMSP001T-RNNNG