

CATALOG LISTING
PAGE | OF |
21HE309 | 0F |
RELEASE NO. PR-23420 |
REPLACES |
REVISIONS




ISSUE
M
4

CHECK
27JAN00

CHECK
27JAN00

CHECK
27JAN00

PTC / CAD
DRAWN
TSM
27JAN00



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

THIRD ANGLE PROJECTION

SCALE **FULL**

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) \pm .030

TWO PLACE (.00) \pm .015

THREE PLACE (.000) \pm .005

ANGLES \pm

WEIGHT 12 OZ MAX

NOTES

1 - CORROSIVE RESISTANT STEEL ENCLOSURE

2 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 5

3 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
4 - TO ADJUST ROLLER DIRECTION, REMOVE ROLLER GUIDE LOCK RING, SCREW ROLLER GUIDE DOWN AS FAR AS POSSIBLE, THEN UNSCREW TO DESIRED DIRECTION. SECURE BY REPLACING ROLLER GUIDE LOCK RING

5 - COINCIDENCE OF OPERATING AND RELEASING POINTS:

.010 INCH OF PLUNGER TRAVEL

6 - FOR OPERATION IN TEMPERATURES OF -65° TO +257°

7 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805

ANSI Y14.5M-1982 APPLIES

