


FACE VIEW - FEMALE



1	BROWN
2	WHITE
3	BLUE
4	BLACK

MOLEX SAP P/N#	ENGINEERING P/N#	"L" (Meters)	"L" (FEET)	TOLERANCE (INCH)
1200652358	804000KF3M050N	5.0 M	16' 5"	+6.50"/-0.00"
1200652359	804000KF3M100N	10.0 M	32' 10"	+12.50"/-0.00"

SPECIFICATIONS:

COUPLING NUT MATERIAL: ZINC DIECAST
WITH BLACK ELECTROPHORETIC COATING
CONTACT MATERIAL: GOLD/NICKEL OVER COPPER ALLOY
INSERT MATERIAL: BLACK NYLON
OVERMOLD MATERIAL: YELLOW TPE
O-RING MATERIAL: VITON

CABLE: #18/4 YELLOW TPE
10 MILLION CYCLE HI-FLEX
PLTC & FT4 RATED

ASSEMBLY RATING: 250V, 4A

ENVIRONMENTAL: -20°C TO 105°C
IP67 WHEN MATED

AGENCY: UL LISTED

RELEASED
EC NO: IPG2015-1677 2015/03/24
DRWN: RSTONE 2015/03/26
CHKD: BARDEN 2015/04/20
APPR: JFMURPHY
DESCRIPTION
A
REV

QUALITY SYMBOLS
▼=0
Ⓒ=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±---
2 PLACES	±---	±.01
1 PLACE	±---	±---
ANGULAR ±---°		

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE: INCH
SCALE: ---
DESIGN UNITS: INCH
THIRD ANGLE PROJECTION

DRAWN BY: RSTONE DATE: 2015/03/24
CHECKED BY: BARDEN DATE: 2015/03/26
APPROVED BY: JFMURPHY DATE: 2015/04/20
MATERIAL NO.: SEE CHART

TITLE
MIC CORDSET ASSEMBLY
4P FEMALE STRAIGHT
18/4 TPE CABLE

molex MOLEX INCORPORATED

DOCUMENT NO.: SD-120065-102
SHEET NO.: 1 OF 1

SIZE B

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

Downloaded from Arrow.com.