



Part Number : [1300940510](#)
Product Description : Bus-Drop Support Grip,
Locking Bale, Cable Diameter 5.59-8.13mm
(.220-.320"), Approximate Break Strength 498.95kg
(1100 lbs)
Series Number : 130094
Status : Active
Product Category : Cable Grips
Engineering Part Number : 36580



Documents and Resources

Drawings

- [1300940510_sd.pdf](#)
- [PK-130227-004-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Bus-Drop Support Grip, Locking Bale, Cable Diameter 5.59-8.13mm (.220-.320"), Approximate Break Strength 498.95kg (1100 lbs)
Product Name	Bus-Drop
Type	Support Grip
UPC	78678836580

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	498.95kg (1100 lbs)
Bale Length	0.305m (12.00")
Body Style	Straight
Cable Diameter	5.59-8.13mm (.220-.320")
Color - Grommet	N/A
Eye Type	Locking Bale
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.089m (3.50")
Net Weight	39.296/g

Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

This document was generated on May 20, 2026