

Set Han3A M receptacle 2x LC dup. MM GOF



Image is for illustration purposes only. Please refer to product description.

Part number	09 57 467 0004 000
Specification	Set Han3A M receptacle 2x LC dup. MM GOF
HARTING eCatalogue	https://b2b.harting.com/09574670004000

Identification

Category	Connectors
Series	LC duplex
Element	Panel feed through
Type of contact	LC contact
Description of the contact	Multimode

Version

Size	Han [®] 3 A
Number of contacts	4

Technical characteristics

Limiting temperature	-40 ... +70 °C
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No



Pushing Performance

Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	No
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
	Lead
	Antimony trioxide
	Naphthalene

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	51.2 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440101 Rectangular connectors (set)