
Product Line

- DeepTronica
- Single Pair Ethernet
- ZConnect
  - Socket
  - Plug
- Ceres
- X-Lok
- M Series
- FLOS & FLOS+
- Power
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
- RJ
- USB
- SSL
- HDMI
- DVI
- Fiber Optic
- RF
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub
- ALTW Emporium





ZA-ACNMAN-BN0001

- Operating Temperature: -40°C ~ +110°C
- Transmission Speed: N/A
- Shielded: Plastic, Non-shielded
- Jacket Material: N/A
- Certificate: N/A

You must login first for view the price

Quantity − 1 + Check Stock

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type ▾ Search



ZConnect, Socket,... ZA-12CFRS-... -40°C ~ +110°C — 0

ZConnect, Socket,... ZA-18BFRS-... -40°C ~ +110°C — 0

ZConnect, Socket,... ZA-36AFRS-... -40°C ~ +110°C — 0

Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current **1A**	Connector Type **Plug**
Shielded **Plastic, Non-shielded**	No. of Contacts **N/A**
Connector Gender **Male**	Backshell **N/A**
Mating Style **Quick Lock**	IP Rating **N/A**
Assembly Style **N/A**	

More Options

People Also Bought



ZA-ACNMAN-BN0001 | 8-03BMMM-SR7A03 | M12A-04PMMR-... | 105-03AFMM-SR7A03 | M12A-05PFFC-...

Downloaded from Arrow.com.