

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -





ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECR-15-012173, RELEASE TO PRODUCTION	18AUG2015	GF	SM
	A1	ECR-15-012490, UPDATE NOTE DESCRIPTION	24AUG2015	GF	SM


NOTES :

1. MATERIALS AND FINISH:
- CONTACTS: COPPER ALLOY, FINISH: TIN OVER NICKEL UNDERPLATE
2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)
3. WIRE TYPES AND SIZES ACCEPTED
WIRE SIZE: 16AWG SOLID
18AWG SOLID & STRANDED (CONDUCTOR NO:16)
20AWG SOLID & STRANDED (CONDUCTOR NO:7)
MAX INSULATION OD: 2.1mm MAX.
STRIP LENGTH: 7.0 +/- 0.3mm
4. PACKAGED IN TAPE AND REEL



SCALE 10:1

P/N: 2834012-3



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN GEORGE FU 24AUG2015

CHK SHI MING 24AUG2015

APVD XU XIANG 24AUG2015

PRODUCT SPEC

108-137049

APPLICATION SPEC

114-137049

WEIGHT -

CUSTOMER DRAWING

STE TE Connectivity		NAME	
SLIM CONTACT		SIZE	RESTRICTED TO
CAGE CODE	DRAWING NO	-	
A3	©=2834012	-	
SCALE 10:1		SHEET 1 OF 1	REV A1

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±-
	1 PLC ±0.20
	2 PLC ±0.13
	3 PLC ±-
	4 PLC ±-
	ANGLES ±-
MATERIAL	FINISH
1	1