


PRODUCT NUMBER	SYMBOL	LENGTH	L1	CUSTOMER P/N
10122956-023PDLF	PD	SEE TABLE	120	3710-081641-M11F
10122956-023PELF	PE	SEE TABLE	100	3710-081636-M21F



COMPONENT LIST OF EACH CABLE

ITEM	DESCRIPTION	SUPPLIER P/N, OR EQUIVALENT	Q'TY	MATERIAL	REMARK
①	PVC WIRE, 16 AWG, UL1430, 105°C 300V				UL CSA APPROVAL
②	CABLE TIE		2	PA66, UL94V-2	
③	HSG	FCI 10122956-H08002	1	PA66, 94V-0, NATURAL	
④	COVER	FCI 10122956-BC0801	1	PA66, 94V-0, NATURAL	
⑤	RECEPTACLE CRIMP TERMINAL, HCC	FCI 10130517-121LF	8	COPPER ALLOY, TIN PLATED	
⑥	DIP-IN TYPE TERMINAL	WELI SHENG H13003PS-2#	2	PHBR, TIN PLATED	FOR PCB HOLE ø4.0
⑦	HS TUBE, ø6mm*10mm		2	EVA, UL 94V-0	125°, BLACK, UL APPROVAL
⑧	LABEL, 12mmX40mm		1		

mat'l. code				surface	tolerance	projection	product family			
ltr				ecn no	dr	date	MINITEK PWR4.2			
A				TAI	2015-08-14		title			
				angles	linear		RIGHT ANGLE WIRE OUTLET CABLE ASSEMBLY, 8 POS.			
				dr	KENNY TAI	2015-03-11	scale			
				engr	KENNY TAI	2015-03-11	dwg no			
				chr	KENNY TAI	2015-08-14	sheet 1 of 1			
				appd	PM ZHENG	2015-08-14	10122956-023XXLF			
sheet index				revision	A		type			
1							CUSTOMER Drawing			