


HONEYWELL PART NUMBER
41SM1-T2
PRODUCT CODE TYC0180


REV	DOCUMENT	CHANGED BY	CHECK
9	0038112	KVS 04JUN08	ASD



- NOTES
- △-MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ±.002 CENTERS
 - 2- TERMINALS ARE PLATED FOR SOLDERING
 - 3- SWITCH WILL WITHSTAND TEMPERATURE OF 250° F

RELEASE NO. SR - 11340

REPLACES -

CHARACTERISTICS	ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 		DRAWN	VK	24 OCT 07	Honeywell		
OPERATING FORCE — — — 3-5 OZ	CONTACT ARRANGEMENT S P D T					CHECK	RJ	24 OCT 07			
RELEASE FORCE — — — — 1 OZ MIN	APPROVALS	KEMA, CE	11A 250V ~ T85 1E4 5A 30 Vdc T85 1E4 		- 0.030 0.015 0.005 - 						