
Part Number : 194300001
Product Description : See and Splice 2 Circuit Push-in Wire Connector for 22-12 AWG Wire, Carton
Series Number : 19430
Status : Active
Product Category : Splices
Engineering Part Number : PC2-RED



Documents and Resources

Drawings

194300001_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per ED/88/2018 (15 January 2019)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Splices
Series	19430
Description	See and Splice 2 Circuit Push-in Wire Connector for 22-12 AWG Wire, Carton
Comments	Red Insert, 1000V max. for lighting/sign fixtures
Product Name	See and Splice
Type	See and Splice
UPC	822348218882

Agency

UL	E32244

Electrical

Voltage - Maximum	600V

Physical

Barrel Type	Closed
Color - Resin	Red
Flammability	94V-2
Insulation	None
Material - Metal	Brass
Material - Plating Mating	N/A
Net Weight	1.736/g
Packaging Type	Carton
Temperature Range - Operating	-30° to +105°C
Wire Insulation Diameter	3.30mm nominal O.D.
Wire Size (AWG)	12, 14, 16, 18, 20, 22

Downloaded from Arrow.com.

Downloaded from Arrow.com.