

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0845110004

Status: Active

Overview: XRC (Extra Rugged Circular) Sealed Plugs and Receptacles

Description: XRC Sealed Receptacle with Pin Insert, Shell Size 24, 31 Circuits, without Collar

Documents:

3D Model	Product Specification PS-84501-001-001 (PDF)
3D Model (PDF)	Packaging Specification PK-84501-001-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E152602
General	
Product Family	Crimp Housings
Series	84511
Application	Power, Wire-to-Wire
Comments	See Product Specification, See Product Specification
Overview	XRC (Extra Rugged Circular) Sealed Plugs and Receptacles
Product Name	XRC
UPC	883906514969
Physical	
Circuits (maximum)	31
Circuits Detail	31
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Net Weight	45.870/g
Number of Rows	0
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	N/A
Pitch - Termination Interface	N/A
Temperature Range - Operating	-40° to +130°C
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-84501-001-001
Product Specification	PS-84501-001-001
Sales Drawing	SD-84511-002-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Relevant	
REACH SVHC	
Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
84511 Series

Mates With
84510 Plug

Use With
84524 XRC Sealed Terminal Pin

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION