

Part Number : [1300100498](#)

Product Description : Mini-Change A-Size Double-Ended Cordset, 3 Poles, Male (Straight) to Female (Straight), 16 AWG, Yellow TPE Cable, 30.0m (98.40') Length

Series Number : 130010

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 113030K13M300




Documents and Resources

Drawings

[1300100498_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; bis(2-ethylhexyl) tetrabromophthalate covering any of the individual isomers and/or combinations thereof per D(2025)4165-DC (25 June 2025) SCIP:0b74de52-6eae-45c3-8b88-bc3fa708da2f
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130010
Description	Mini-Change A-Size Double-Ended Cordset, 3 Poles, Male (Straight) to Female (Straight), 16 AWG, Yellow TPE Cable, 30.0m (98.40') Length
IP Rating	IP67
Product Name	Mini-Change
Protocol	DeviceNet
Type	Double Ended
UPC	78678884072

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	13.0A
Voltage - Maximum	600V

Physical

Cable Diameter	10.41mm (.410")
Cable Length	30.0m (98.40')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change
Connector End B	Mini-Change
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	1875.000/g
Orientation	Straight to Straight
Poles	3
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	TC-ER
Wire Size (AWG)	16

This document was generated on Apr 23, 2026