

har-port USB 2.0 A-A; PFT



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 452 1901
Specification	har-port USB 2.0 A-A; PFT
HARTING eCatalogue	https://b2b.harting.com/09454521901

Identification

Category	Connectors
Series	har-port
Element	Service interfaces
Specification	USB 2.0

Version

Connection type	Type A jack - type A jack
Fixing	Screwable in cover plates

Technical characteristics

Ambient temperature	-25 ... +70 °C
Mating cycles	≥1,500
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	Silver
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	No
-----------------------	----

Specifications and approvals

Specifications	EN 45545-2
Approvals	DNV GL
UL / CSA	UL 1863 DUXR2.E470046 CSA-C22.2 No. 182.4, No. 233-09 DUXR8.E470046

Commercial data

Packaging size	1
Net weight	13.9 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27060304 Appliance cord (data cable)