Data sheet

BUGH WM4 C BT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



WM4 C photovoltaic connectors
- one crimp contact for 4 mm² and 6 mm² cables
- TÜV approval according to the latest standard IEC 62852
- Can be loaded with a rated current of up to 35 A

General ordering data

Version	Photovoltaics, Plug-in connector, female
Order No.	1530690000
Type	BUGH WM4 C BT
GTIN (EAN)	4050118335347
Qty.	100 items

Downloaded from Arrow.com.

Data sheet

BUGH WM4 C BT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform

Dimensions and weights

Net weight	11.6 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Outer cable diameter, max.	7 mm	Outer cable diameter, min.	5.5 mm
Cable type	2 Pfg1169/08.07, EN 50618:2014	Approvals	TÜV Rheinland (IEC 62852)
Conductor cross-section, max.	6 mm²	Conductor cross-section, min.	4 mm²
Protection degree	IP65, IP67, IP2x open	Pollution severity	3 (2 within the sealed area)
Rated voltage	1500 V DC (IEC)	External thread	M 16
Rated current	35 A		

Guarantee

Time interval	2 years

Important note

Product information	Please order contacts separately

Classifications

ETIM 8.0	EC002928	ETIM 9.0	EC002928
ETIM 10.0	EC002928	ECLASS 14.0	22-57-02-92
ECLASS 15.0	22-57-02-92		

Downloaded from Arrow.com.