**Part Number :** 192120003
**Product Description :** InsulKrimp  Wire Pin Terminal for 22-18 AWG Wire, Bag
**Series Number :** 19212
**Status :** Active
**Product Category :** Crimp Terminals
**Engineering Part Number :** WP-2218X



## Documents and Resources

### Drawings

192120003_sd.pdf

### Specifications

PS-19902-011-001.pdf

PS-19902-013-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Crimp Terminals |
| Series | 19212 |
| Description | InsulKrimp  Wire Pin Terminal for 22-18 AWG Wire, Bag |
| Application | Wire-to-Component |
| Comments | Pin Length 8.90mm |
| Product Name | Wire Pin,InsulKrimp |
| UPC | 800753053335 |

### Agency

| | |
|---|---|
| CSA | LR18689 |
| UL | E32244 |

### Physical

| | |
|---|---|
| Flammability | 94V-0 |
| Gender | Male |
| Material - Metal | Copper |
| Material - Plating Mating | Tin |
| Net Weight | 0.689/g |
| Packaging Type | Bag |
| Plating min - Mating | 1.016µm |
| Termination Interface Style | Crimp or Compression |
| Wire Insulation Diameter | 3.68mm max. |
| Wire Size (AWG) | 18, 19, 20, 22 |
| Wire Size $mm^2$ | N/A |

## Application Tooling

Downloaded from Arrow.com.

## Global

| Description | Part Number |
| --- | --- |
| PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 22-10 AWG and 6.0-0.5mm² (Rings, Spades, Hooks, Block Spades and Flanged Spades) | 640010100 |
| PremiumGrade Hand Crimp Tool for Insulkrimp Terminals and Splices, 22-10 AWG (Rings, Spades, Hooks, Block Spades and Flanged Spades) | 640010300 |
| Crimp Head for the AT-200 Pneumatic Hand Tool | 640050100 |
| Crimp Head for the AT-200 Pneumatic Hand Tool | 640050300 |
| ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool | 640160036 |



Downloaded from Arrow.com.